

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839979

Luminaire Tested: **LDS4C35D010 EU4359040 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C35D010 EU4359040 4LBPSMMS
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2826.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839979

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839979

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182302
5°	181679
10°	179676
15°	176587
20°	172626
25°	168019
30°	162726
35°	156455
40°	148570
45°	135084
50°	111522
55°	82120
60°	55726
65°	32645
70°	12895
75°	2895
80°	3750
85°	6484



TEST NUMBER: P839979

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.6	4.9
10°-20°	390.9	13.8
20°-30°	570.3	20.2
30°-40°	650.9	23.0
40°-50°	591.8	20.9
50°-60°	349.0	12.3
60°-70°	117.0	4.1
70°-80°	12.2	0.4
80°-90°	4.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.8	39.0
0°-40°	1751.7	62.0
0°-60°	2692.5	95.3
0°-90°	2826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2826.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1484	
5°	1473	140
15°	1388	391
25°	1240	570
35°	1043	651
45°	778	592
55°	383	349
65°	112	117
75°	6	12
85°	5	4
90°	0	



TEST NUMBER: P839979

CATALOG NUMBER: LDS4C35D010 EU4359040 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1483.9
2.5°	1481.6
5°	1473.2
7.5°	1459.4
10°	1440.3
12.5°	1415.9
15°	1388.4
17.5°	1356.3
20°	1320.4
22.5°	1281.5
25°	1239.5
27.5°	1193.7
30°	1147.1
32.5°	1095.9
35°	1043.2
37.5°	985.9
40°	926.4
42.5°	856.9
45°	777.5
47.5°	685.8
50°	583.5
52.5°	481.1
55°	383.4
57.5°	300.1
60°	226.8
62.5°	164.2
65°	112.3
67.5°	68.7
70°	35.9
72.5°	13.7
75°	6.1
77.5°	6.1
80°	5.3
82.5°	4.6
85°	4.6
87.5°	3.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)