

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857225

Luminaire Tested: **LX4C20D010 EX4C209730 4LBWH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P857225  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C20D010 EX4C209730 4LBWH  
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 97CRI LEDS  
AND 4LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1665.0 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857225

CATALOG NUMBER: LX4C20D010 EX4C209730 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P857225

CATALOG NUMBER: LX4C20D010 EX4C209730 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 97  | 96  | 96  | 94  | 93  | 91  |    |    | 91  |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 95  | 91  | 88  | 91  | 88  | 86  | 89  | 86  | 84  | 82  |    |    | 82  |
| 3   | 99  | 91  | 85  | 80  | 97  | 90  | 84  | 80  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    | 74  |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |    |    | 67  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 64  | 74  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 61  |    |    | 61  |
| 6   | 81  | 71  | 64  | 58  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 61  | 57  | 65  | 61  | 57  | 55  |    |    | 55  |
| 7   | 76  | 65  | 58  | 53  | 75  | 65  | 58  | 53  | 63  | 57  | 53  | 62  | 56  | 52  | 61  | 56  | 52  | 50  |    |    | 50  |
| 8   | 72  | 60  | 53  | 49  | 70  | 60  | 53  | 49  | 59  | 53  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 46  |    |    | 46  |
| 9   | 68  | 56  | 49  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 43  |    |    | 43  |
| 10  | 64  | 52  | 46  | 41  | 63  | 52  | 46  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 49  | 44  | 41  | 39  |    |    | 39  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 131846 |
| 5°  | 132350 |
| 10° | 132745 |
| 15° | 132758 |
| 20° | 132032 |
| 25° | 128939 |
| 30° | 120509 |
| 35° | 104354 |
| 40° | 81518  |
| 45° | 58499  |
| 50° | 37996  |
| 55° | 22747  |
| 60° | 13317  |
| 65° | 8546   |
| 70° | 5675   |
| 75° | 4272   |
| 80° | 3184   |
| 85° | 0      |



TEST NUMBER: P857225

CATALOG NUMBER: LX4C20D010 EX4C209730 4LBWH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 102.2  | 6.1       |
| 10°-20°   | 294.5  | 17.7      |
| 20°-30°   | 434.6  | 26.1      |
| 30°-40°   | 428.8  | 25.8      |
| 40°-50°   | 262.4  | 15.8      |
| 50°-60°   | 100.6  | 6.0       |
| 60°-70°   | 31.5   | 1.9       |
| 70°-80°   | 9.2    | 0.6       |
| 80°-90°   | 1.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 831.2  | 49.9      |
| 0°-40°    | 1260.1 | 75.7      |
| 0°-60°    | 1623.1 | 97.5      |
| 0°-90°    | 1665.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1665.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1073 |      |
| 5°  | 1073 | 102  |
| 15° | 1044 | 294  |
| 25° | 951  | 435  |
| 35° | 696  | 429  |
| 45° | 337  | 262  |
| 55° | 106  | 101  |
| 65° | 29   | 31   |
| 75° | 9    | 9    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P857225

CATALOG NUMBER: LX4C20D010 EX4C209730 4LBWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1073.2 |
| 2.5°  | 1075.5 |
| 5°    | 1073.2 |
| 7.5°  | 1070.9 |
| 10°   | 1064.1 |
| 12.5° | 1055.1 |
| 15°   | 1043.8 |
| 17.5° | 1030.2 |
| 20°   | 1009.9 |
| 22.5° | 987.4  |
| 25°   | 951.2  |
| 27.5° | 905.9  |
| 30°   | 849.5  |
| 32.5° | 779.5  |
| 35°   | 695.8  |
| 37.5° | 603.2  |
| 40°   | 508.3  |
| 42.5° | 420.2  |
| 45°   | 336.7  |
| 47.5° | 262.0  |
| 50°   | 198.8  |
| 52.5° | 146.9  |
| 55°   | 106.2  |
| 57.5° | 74.5   |
| 60°   | 54.2   |
| 62.5° | 40.7   |
| 65°   | 29.4   |
| 67.5° | 22.6   |
| 70°   | 15.8   |
| 72.5° | 11.3   |
| 75°   | 9.0    |
| 77.5° | 4.5    |
| 80°   | 4.5    |
| 82.5° | 2.3    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)