

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857228

Luminaire Tested: **LX4C20D010 EX4C209827 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209827 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1214.6 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857228

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857228

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 77 | 73 | 81 | 76 | 73 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | | | |
| 6 | 88 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | | | |
| 9 | 76 | 66 | 60 | 56 | 74 | 65 | 60 | 56 | 64 | 59 | 56 | 64 | 59 | 56 | 63 | 58 | 55 | 54 | | | |
| 10 | 72 | 62 | 57 | 53 | 71 | 62 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 60 | 55 | 52 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 179759 |
| 5° | 177326 |
| 10° | 169010 |
| 15° | 156389 |
| 20° | 140792 |
| 25° | 116956 |
| 30° | 85016 |
| 35° | 55116 |
| 40° | 33358 |
| 45° | 17183 |
| 50° | 7798 |
| 55° | 4669 |
| 60° | 3145 |
| 65° | 2267 |
| 70° | 1688 |
| 75° | 1092 |
| 80° | 707 |
| 85° | 564 |



TEST NUMBER: P857228

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 134.6 | 11.1 |
| 10°-20° | 343.1 | 28.2 |
| 20°-30° | 388.0 | 31.9 |
| 30°-40° | 234.5 | 19.3 |
| 40°-50° | 82.2 | 6.8 |
| 50°-60° | 21.0 | 1.7 |
| 60°-70° | 8.1 | 0.7 |
| 70°-80° | 2.7 | 0.2 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 865.7 | 71.3 |
| 0°-40° | 1100.2 | 90.6 |
| 0°-60° | 1203.4 | 99.1 |
| 0°-90° | 1214.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1214.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1463 | |
| 5° | 1438 | 135 |
| 15° | 1230 | 343 |
| 25° | 863 | 388 |
| 35° | 368 | 234 |
| 45° | 99 | 82 |
| 55° | 22 | 21 |
| 65° | 8 | 8 |
| 75° | 2 | 3 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P857228

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1463.2 |
| 2.5° | 1457.1 |
| 5° | 1437.9 |
| 7.5° | 1404.0 |
| 10° | 1354.8 |
| 12.5° | 1295.6 |
| 15° | 1229.6 |
| 17.5° | 1157.3 |
| 20° | 1076.9 |
| 22.5° | 978.2 |
| 25° | 862.8 |
| 27.5° | 730.6 |
| 30° | 599.3 |
| 32.5° | 473.8 |
| 35° | 367.5 |
| 37.5° | 278.7 |
| 40° | 208.0 |
| 42.5° | 149.5 |
| 45° | 98.9 |
| 47.5° | 60.9 |
| 50° | 40.8 |
| 52.5° | 29.2 |
| 55° | 21.8 |
| 57.5° | 16.9 |
| 60° | 12.8 |
| 62.5° | 10.1 |
| 65° | 7.8 |
| 67.5° | 6.1 |
| 70° | 4.7 |
| 72.5° | 3.4 |
| 75° | 2.3 |
| 77.5° | 1.7 |
| 80° | 1.0 |
| 82.5° | 0.7 |
| 85° | 0.4 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)