

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857258

Luminaire Tested: **LX4C20D010 EX4C209835 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209835 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1125.5 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857258

CATALOG NUMBER: LX4C20D010 EX4C209835 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857258

CATALOG NUMBER: LX4C20D010 EX4C209835 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173592
5°	169717
10°	156934
15°	140809
20°	123953
25°	106681
30°	85910
35°	57186
40°	29749
45°	13465
50°	5848
55°	3920
60°	2531
65°	1802
70°	1473
75°	997
80°	0
85°	0



TEST NUMBER: P857258

CATALOG NUMBER: LX4C20D010 EX4C209835 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	11.3
10°-20°	309.2	27.5
20°-30°	359.0	31.9
30°-40°	237.8	21.1
40°-50°	66.7	5.9
50°-60°	16.8	1.5
60°-70°	6.3	0.6
70°-80°	2.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.7	70.7
0°-40°	1033.5	91.8
0°-60°	1116.9	99.2
0°-90°	1125.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1125.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1413	
5°	1376	127
15°	1107	309
25°	787	359
35°	381	238
45°	78	67
55°	18	17
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P857258

CATALOG NUMBER: LX4C20D010 EX4C209835 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1413.0
2.5°	1406.8
5°	1376.2
7.5°	1323.2
10°	1258.0
12.5°	1184.5
15°	1107.1
17.5°	1031.7
20°	948.1
22.5°	870.6
25°	787.0
27.5°	707.5
30°	605.6
32.5°	497.5
35°	381.3
37.5°	273.2
40°	185.5
42.5°	120.3
45°	77.5
47.5°	46.9
50°	30.6
52.5°	22.4
55°	18.3
57.5°	14.3
60°	10.3
62.5°	8.2
65°	6.2
67.5°	4.1
70°	4.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)