

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840006

Luminaire Tested: **LDS4C40D010 EU4409030 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P840006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C40D010 EU4409030 4LBCSMB
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2781.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840006

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P840006

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179403
5°	178781
10°	176819
15°	173776
20°	169881
25°	165349
30°	160130
35°	153966
40°	146197
45°	132929
50°	109745
55°	80813
60°	54842
65°	32122
70°	12680
75°	2848
80°	3750
85°	6343



TEST NUMBER: P840006

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	4.9
10°-20°	384.7	13.8
20°-30°	561.2	20.2
30°-40°	640.5	23.0
40°-50°	582.3	20.9
50°-60°	343.5	12.4
60°-70°	115.2	4.1
70°-80°	12.0	0.4
80°-90°	4.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1083.3	39.0
0°-40°	1723.8	62.0
0°-60°	2649.6	95.3
0°-90°	2781.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2781.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1460	
5°	1450	137
15°	1366	385
25°	1220	561
35°	1027	641
45°	765	582
55°	377	343
65°	110	115
75°	6	12
85°	4	4
90°	0	



TEST NUMBER: P840006

CATALOG NUMBER: LDS4C40D010 EU4409030 4LBCSMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1460.3
2.5°	1458.0
5°	1449.7
7.5°	1436.2
10°	1417.4
12.5°	1393.4
15°	1366.3
17.5°	1334.7
20°	1299.4
22.5°	1261.1
25°	1219.8
27.5°	1174.7
30°	1128.8
32.5°	1078.5
35°	1026.6
37.5°	970.2
40°	911.6
42.5°	843.2
45°	765.1
47.5°	674.9
50°	574.2
52.5°	473.5
55°	377.3
57.5°	295.4
60°	223.2
62.5°	161.6
65°	110.5
67.5°	67.6
70°	35.3
72.5°	13.5
75°	6.0
77.5°	6.0
80°	5.3
82.5°	4.5
85°	4.5
87.5°	3.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)