

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857276

Luminaire Tested: **LX4C20D010 EX4C209840 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209840 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1507.9 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857276

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857276

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119414
5°	119870
10°	120233
15°	120230
20°	119573
25°	116766
30°	109146
35°	94515
40°	73836
45°	52974
50°	34403
55°	20584
60°	12040
65°	7762
70°	5172
75°	3892
80°	2901
85°	0



TEST NUMBER: P857276

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	6.1
10°-20°	266.7	17.7
20°-30°	393.6	26.1
30°-40°	388.4	25.8
40°-50°	237.7	15.8
50°-60°	91.1	6.0
60°-70°	28.5	1.9
70°-80°	8.4	0.6
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.8	49.9
0°-40°	1141.2	75.7
0°-60°	1469.9	97.5
0°-90°	1507.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1507.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	972	
5°	972	93
15°	945	267
25°	861	394
35°	630	388
45°	305	238
55°	96	91
65°	27	28
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P857276

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	972.0
2.5°	974.0
5°	972.0
7.5°	969.9
10°	963.8
12.5°	955.6
15°	945.3
17.5°	933.0
20°	914.6
22.5°	894.2
25°	861.4
27.5°	820.5
30°	769.4
32.5°	706.0
35°	630.2
37.5°	546.3
40°	460.4
42.5°	380.6
45°	304.9
47.5°	237.3
50°	180.0
52.5°	133.0
55°	96.1
57.5°	67.5
60°	49.0
62.5°	36.8
65°	26.7
67.5°	20.5
70°	14.4
72.5°	10.3
75°	8.2
77.5°	4.1
80°	4.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)