

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840019

Luminaire Tested: **LDS4C40D010 EU4409035 4LBPSMMS**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P840019  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C40D010 EU4409035 4LBPSMMS  
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBPS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3275.9 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840019

CATALOG NUMBER: LDS4C40D010 EU4409035 4LBPSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P840019

CATALOG NUMBER: LDS4C40D010 EU4409035 4LBPSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	211333
5°	210611
10°	208293
15°	204708
20°	200121
25°	194777
30°	188630
35°	181366
40°	172225
45°	156593
50°	129278
55°	95185
60°	64596
65°	37820
70°	14943
75°	3370
80°	4386
85°	7471



TEST NUMBER: P840019

CATALOG NUMBER: LDS4C40D010 EU4409035 4LBPSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.8	4.9
10°-20°	453.2	13.8
20°-30°	661.1	20.2
30°-40°	754.5	23.0
40°-50°	686.0	20.9
50°-60°	404.6	12.3
60°-70°	135.7	4.1
70°-80°	14.2	0.4
80°-90°	4.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.1	39.0
0°-40°	2030.6	62.0
0°-60°	3121.2	95.3
0°-90°	3275.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3275.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1720	
5°	1708	162
15°	1610	453
25°	1437	661
35°	1209	755
45°	901	686
55°	444	405
65°	130	136
75°	7	14
85°	5	5
90°	0	



TEST NUMBER: P840019

CATALOG NUMBER: LDS4C40D010 EU4409035 4LBPSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1720.2
2.5°	1717.5
5°	1707.8
7.5°	1691.8
10°	1669.7
12.5°	1641.4
15°	1609.5
17.5°	1572.3
20°	1530.7
22.5°	1485.6
25°	1436.9
27.5°	1383.7
30°	1329.7
32.5°	1270.4
35°	1209.3
37.5°	1142.9
40°	1073.9
42.5°	993.3
45°	901.3
47.5°	795.0
50°	676.4
52.5°	557.7
55°	444.4
57.5°	347.9
60°	262.9
62.5°	190.3
65°	130.1
67.5°	79.7
70°	41.6
72.5°	15.9
75°	7.1
77.5°	7.1
80°	6.2
82.5°	5.3
85°	5.3
87.5°	4.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)