

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857308

Luminaire Tested: **LX4C20D010 EX4C209030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209030 4LBMH
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1767.5 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 32.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857308

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857308

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139979
5°	140514
10°	140929
15°	140936
20°	140164
25°	136882
30°	127928
35°	110788
40°	86538
45°	62095
50°	40347
55°	24139
60°	14128
65°	9070
70°	6035
75°	4557
80°	3467
85°	0



TEST NUMBER: P857308

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	6.1
10°-20°	312.6	17.7
20°-30°	461.3	26.1
30°-40°	455.2	25.8
40°-50°	278.6	15.8
50°-60°	106.8	6.0
60°-70°	33.4	1.9
70°-80°	9.8	0.6
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.4	49.9
0°-40°	1337.7	75.7
0°-60°	1723.1	97.5
0°-90°	1767.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1767.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1139	
5°	1139	108
15°	1108	313
25°	1010	461
35°	739	455
45°	357	279
55°	113	107
65°	31	33
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P857308

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1139.4
2.5°	1141.7
5°	1139.4
7.5°	1136.9
10°	1129.7
12.5°	1120.1
15°	1108.1
17.5°	1093.7
20°	1072.1
22.5°	1048.1
25°	1009.8
27.5°	961.8
30°	901.8
32.5°	827.5
35°	738.7
37.5°	640.3
40°	539.6
42.5°	446.1
45°	357.4
47.5°	278.1
50°	211.1
52.5°	156.0
55°	112.7
57.5°	79.1
60°	57.5
62.5°	43.2
65°	31.2
67.5°	23.9
70°	16.8
72.5°	12.0
75°	9.6
77.5°	4.9
80°	4.9
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)