

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857324

Luminaire Tested: **LD4C02D010 EU4029040 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P857324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C02D010 EU4029040 4LBMLI
Description: 4 INCH 250 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 313.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857324

CATALOG NUMBER: LD4C02D010 EU4029040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857324

CATALOG NUMBER: LD4C02D010 EU4029040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			73
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			65
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60616
5°	59590
10°	54752
15°	45851
20°	36737
25°	29510
30°	21974
35°	12553
40°	5886
45°	2502
50°	803
55°	407
60°	270
65°	233
70°	144
75°	0
80°	0
85°	0



TEST NUMBER: P857324

CATALOG NUMBER: LD4C02D010 EU4029040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	14.3
10°-20°	99.9	31.9
20°-30°	99.3	31.7
30°-40°	54.1	17.3
40°-50°	12.5	4.0
50°-60°	1.8	0.6
60°-70°	0.7	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.9	77.9
0°-40°	297.9	95.2
0°-60°	312.2	99.7
0°-90°	313.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	313.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	493	
5°	483	45
15°	360	100
25°	218	99
35°	84	54
45°	14	12
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857324

CATALOG NUMBER: LD4C02D010 EU4029040 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	493.4
2.5°	492.3
5°	483.2
7.5°	464.6
10°	438.9
12.5°	401.0
15°	360.5
17.5°	320.4
20°	281.0
22.5°	248.8
25°	217.7
27.5°	188.2
30°	154.9
32.5°	117.8
35°	83.7
37.5°	56.4
40°	36.7
42.5°	23.1
45°	14.4
47.5°	8.3
50°	4.2
52.5°	2.3
55°	1.9
57.5°	1.1
60°	1.1
62.5°	0.8
65°	0.8
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)