

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857358

Luminaire Tested: **LX4C25D010 EX4C259030 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259030 4LBMDH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1779.0 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857358

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857358

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	63	60	68	63	59	67	62	59	66	62	59	57		
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263300
5°	259742
10°	247564
15°	229077
20°	206213
25°	171313
30°	124538
35°	80732
40°	48850
45°	25175
50°	11391
55°	6854
60°	4595
65°	3285
70°	2478
75°	1661
80°	1061
85°	705



TEST NUMBER: P857358

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.2	11.1
10°-20°	502.6	28.3
20°-30°	568.3	31.9
30°-40°	343.5	19.3
40°-50°	120.3	6.8
50°-60°	30.8	1.7
60°-70°	11.8	0.7
70°-80°	4.0	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1268.1	71.3
0°-40°	1611.6	90.6
0°-60°	1762.6	99.1
0°-90°	1779.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1779.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2143	
5°	2106	197
15°	1801	503
25°	1264	568
35°	538	343
45°	145	120
55°	32	31
65°	11	12
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P857358

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2143.2
2.5°	2134.3
5°	2106.2
7.5°	2056.4
10°	1984.5
12.5°	1897.7
15°	1801.1
17.5°	1695.1
20°	1577.3
22.5°	1432.9
25°	1263.8
27.5°	1070.1
30°	877.9
32.5°	694.0
35°	538.3
37.5°	408.1
40°	304.6
42.5°	218.9
45°	144.9
47.5°	89.2
50°	59.6
52.5°	42.9
55°	32.0
57.5°	24.6
60°	18.7
62.5°	14.8
65°	11.3
67.5°	8.9
70°	6.9
72.5°	4.9
75°	3.5
77.5°	2.5
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)