

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857379

Luminaire Tested: **LX4C25D010 EX4C259035 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259035 4LBMDH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1804.0 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857379

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857379

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	63	60	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266997
5°	263393
10°	251032
15°	232295
20°	209115
25°	173726
30°	126283
35°	81857
40°	49539
45°	25540
50°	11563
55°	6961
60°	4668
65°	3343
70°	2514
75°	1661
80°	1061
85°	705



TEST NUMBER: P857379

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	11.1
10°-20°	509.7	28.3
20°-30°	576.3	31.9
30°-40°	348.3	19.3
40°-50°	122.0	6.8
50°-60°	31.2	1.7
60°-70°	12.0	0.7
70°-80°	4.0	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.9	71.3
0°-40°	1634.2	90.6
0°-60°	1787.4	99.1
0°-90°	1804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1804.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2173	
5°	2136	200
15°	1826	510
25°	1282	576
35°	546	348
45°	147	122
55°	32	31
65°	12	12
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P857379

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2173.3
2.5°	2164.3
5°	2135.8
7.5°	2085.3
10°	2012.3
12.5°	1924.4
15°	1826.4
17.5°	1718.9
20°	1599.5
22.5°	1453.0
25°	1281.6
27.5°	1085.1
30°	890.2
32.5°	703.8
35°	545.8
37.5°	413.9
40°	308.9
42.5°	221.9
45°	147.0
47.5°	90.5
50°	60.5
52.5°	43.5
55°	32.5
57.5°	25.0
60°	19.0
62.5°	15.0
65°	11.5
67.5°	9.0
70°	7.0
72.5°	5.0
75°	3.5
77.5°	2.5
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)