

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840048

Luminaire Tested: **LDS4C45D010 EU4459027 4LBPSMB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P840048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C45D010 EU4459027 4LBPSMB  
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBPS TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3518.0 lumens  
Efficiency: N/A  
Efficacy: 70.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P840048

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBPSMB

### Luminous Intensity Polar Plot





TEST NUMBER: P840048

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBPSMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	226935
5°	226162
10°	223674
15°	219830
20°	214907
25°	209160
30°	202575
35°	194774
40°	184943
45°	168147
50°	138815
55°	102232
60°	69388
65°	40639
70°	16056
75°	3607
80°	4740
85°	8035



TEST NUMBER: P840048

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBPSMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.8	4.9
10°-20°	486.7	13.8
20°-30°	709.9	20.2
30°-40°	810.3	23.0
40°-50°	736.6	20.9
50°-60°	434.5	12.3
60°-70°	145.7	4.1
70°-80°	15.2	0.4
80°-90°	5.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.3	39.0
0°-40°	2180.7	62.0
0°-60°	3351.8	95.3
0°-90°	3518.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3518.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1847	
5°	1834	174
15°	1728	487
25°	1543	710
35°	1299	810
45°	968	737
55°	477	434
65°	140	146
75°	8	15
85°	6	5
90°	0	



TEST NUMBER: P840048

CATALOG NUMBER: LDS4C45D010 EU4459027 4LBPSMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1847.2
2.5°	1844.4
5°	1833.9
7.5°	1816.8
10°	1793.0
12.5°	1762.6
15°	1728.4
17.5°	1688.5
20°	1643.8
22.5°	1595.3
25°	1543.0
27.5°	1486.0
30°	1428.0
32.5°	1364.3
35°	1298.7
37.5°	1227.4
40°	1153.2
42.5°	1066.7
45°	967.8
47.5°	853.7
50°	726.3
52.5°	598.9
55°	477.3
57.5°	373.6
60°	282.4
62.5°	204.4
65°	139.8
67.5°	85.6
70°	44.7
72.5°	17.1
75°	7.6
77.5°	7.6
80°	6.7
82.5°	5.7
85°	5.7
87.5°	4.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)