

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857389

Luminaire Tested: **LX4C25D010 EX4C259035 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857389  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259035 4LBWLI  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2513.0 lumens  
Efficiency: N/A  
Efficacy: 79.8 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857389

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P857389

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P857389

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.6	6.0
10°-20°	475.2	18.9
20°-30°	741.3	29.5
30°-40°	721.3	28.7
40°-50°	360.3	14.3
50°-60°	55.8	2.2
60°-70°	6.8	0.3
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1367.0	54.4
0°-40°	2088.3	83.1
0°-60°	2504.4	99.7
0°-90°	2513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2513.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1540	
5°	1560	151
15°	1678	475
25°	1629	741
35°	1171	721
45°	452	360
55°	46	56
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P857389

CATALOG NUMBER: LX4C25D010 EX4C259035 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1539.7
2.5°	1545.5
5°	1559.9
7.5°	1582.9
10°	1611.7
12.5°	1649.1
15°	1677.9
17.5°	1700.9
20°	1703.8
22.5°	1683.7
25°	1629.0
27.5°	1548.3
30°	1447.6
32.5°	1321.1
35°	1171.4
37.5°	1007.3
40°	834.6
42.5°	650.5
45°	451.9
47.5°	290.7
50°	175.5
52.5°	95.0
55°	46.1
57.5°	20.2
60°	11.5
62.5°	8.6
65°	5.8
67.5°	5.8
70°	2.9
72.5°	2.9
75°	2.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)