

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P840068

Luminaire Tested: **LDS4C45D010 EU4459035 4LBPSMB**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P840068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C45D010 EU4459035 4LBPSMB
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3708.9 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P840068

CATALOG NUMBER: LDS4C45D010 EU4459035 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P840068

CATALOG NUMBER: LDS4C45D010 EU4459035 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239257
5°	238445
10°	235825
15°	231761
20°	226569
25°	220519
30°	213569
35°	205348
40°	194982
45°	177285
50°	146364
55°	107780
60°	73147
65°	42820
70°	16918
75°	3797
80°	4952
85°	8458



TEST NUMBER: P840068

CATALOG NUMBER: LDS4C45D010 EU4459035 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	4.9
10°-20°	513.1	13.8
20°-30°	748.4	20.2
30°-40°	854.3	23.0
40°-50°	776.7	20.9
50°-60°	458.1	12.4
60°-70°	153.6	4.1
70°-80°	16.0	0.4
80°-90°	5.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1444.7	39.0
0°-40°	2299.0	62.0
0°-60°	3533.7	95.3
0°-90°	3708.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3708.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1948	
5°	1934	183
15°	1822	513
25°	1627	748
35°	1369	854
45°	1020	777
55°	503	458
65°	147	154
75°	8	16
85°	6	6
90°	0	



TEST NUMBER: P840068

CATALOG NUMBER: LDS4C45D010 EU4459035 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1947.5
2.5°	1944.5
5°	1933.5
7.5°	1915.5
10°	1890.4
12.5°	1858.3
15°	1822.2
17.5°	1780.1
20°	1733.0
22.5°	1681.9
25°	1626.8
27.5°	1566.6
30°	1505.5
32.5°	1438.3
35°	1369.2
37.5°	1294.0
40°	1215.8
42.5°	1124.6
45°	1020.4
47.5°	900.1
50°	765.8
52.5°	631.5
55°	503.2
57.5°	393.9
60°	297.7
62.5°	215.5
65°	147.3
67.5°	90.2
70°	47.1
72.5°	18.0
75°	8.0
77.5°	8.0
80°	7.0
82.5°	6.0
85°	6.0
87.5°	5.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)