

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856700

Luminaire Tested: **LX4C10D010 EX4C109027 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P856700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109027 4LBMLI
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 910.0 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856700

CATALOG NUMBER: LX4C10D010 EX4C109027 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P856700

CATALOG NUMBER: LX4C10D010 EX4C109027 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90																											
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																											
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81																											
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77																											
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73																											
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69																											
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																											
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63																											
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	287698
5°	258904
10°	200708
15°	145273
20°	100590
25°	73335
30°	53282
35°	31525
40°	13263
45°	4135
50°	535
55°	300
60°	344
65°	407
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856700

CATALOG NUMBER: LX4C10D010 EX4C109027 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.5	20.3
10°-20°	315.9	34.7
20°-30°	251.1	27.6
30°-40°	132.9	14.6
40°-50°	22.9	2.5
50°-60°	1.7	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.6	82.6
0°-40°	884.5	97.2
0°-60°	909.1	99.9
0°-90°	910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2342	
5°	2099	185
15°	1142	316
25°	541	251
35°	210	133
45°	24	23
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856700

CATALOG NUMBER: LX4C10D010 EX4C109027 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2341.8
2.5°	2281.5
5°	2099.4
7.5°	1861.1
10°	1608.9
12.5°	1365.0
15°	1142.2
17.5°	934.7
20°	769.4
22.5°	643.2
25°	541.0
27.5°	458.3
30°	375.6
32.5°	291.5
35°	210.2
37.5°	138.8
40°	82.7
42.5°	47.7
45°	23.8
47.5°	8.4
50°	2.8
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)