

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856728

Luminaire Tested: **LX4C10D010 EX4C109030 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P856728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109030 4LBSLI
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1032.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856728

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P856728

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 98 | 98 | 96 | 95 | 95 | 93 | 92 | 90 | | | 90 |
| 2 | 104 | 98 | 93 | 88 | 102 | 96 | 91 | 87 | 93 | 89 | 85 | 90 | 86 | 84 | 87 | 84 | 82 | 80 | | | 80 |
| 3 | 97 | 89 | 82 | 77 | 95 | 87 | 81 | 77 | 84 | 79 | 75 | 82 | 78 | 74 | 79 | 76 | 73 | 71 | | | 71 |
| 4 | 90 | 81 | 73 | 68 | 88 | 79 | 73 | 68 | 77 | 71 | 67 | 75 | 70 | 66 | 73 | 69 | 65 | 63 | | | 63 |
| 5 | 84 | 73 | 66 | 61 | 82 | 72 | 65 | 60 | 70 | 64 | 60 | 69 | 63 | 59 | 67 | 62 | 59 | 57 | | | 57 |
| 6 | 79 | 67 | 60 | 54 | 77 | 66 | 59 | 54 | 65 | 58 | 54 | 63 | 58 | 53 | 62 | 57 | 53 | 51 | | | 51 |
| 7 | 74 | 62 | 54 | 49 | 72 | 61 | 54 | 49 | 60 | 53 | 49 | 58 | 53 | 48 | 57 | 52 | 48 | 46 | | | 46 |
| 8 | 69 | 57 | 50 | 45 | 68 | 57 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 44 | 53 | 48 | 44 | 42 | | | 42 |
| 9 | 65 | 53 | 46 | 41 | 64 | 53 | 46 | 41 | 52 | 45 | 41 | 51 | 45 | 41 | 50 | 44 | 41 | 39 | | | 39 |
| 10 | 61 | 50 | 43 | 38 | 60 | 49 | 42 | 38 | 48 | 42 | 38 | 47 | 42 | 38 | 46 | 41 | 37 | 36 | | | 36 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 90531 |
| 5° | 88484 |
| 10° | 83083 |
| 15° | 77304 |
| 20° | 71697 |
| 25° | 65350 |
| 30° | 58176 |
| 35° | 51577 |
| 40° | 46348 |
| 45° | 41489 |
| 50° | 35588 |
| 55° | 28637 |
| 60° | 21327 |
| 65° | 13605 |
| 70° | 6573 |
| 75° | 1092 |
| 80° | 778 |
| 85° | 0 |



TEST NUMBER: P856728

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBSLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 66.8 | 6.5 |
| 10°-20° | 170.4 | 16.5 |
| 20°-30° | 220.8 | 21.4 |
| 30°-40° | 216.4 | 21.0 |
| 40°-50° | 183.4 | 17.8 |
| 50°-60° | 120.2 | 11.7 |
| 60°-70° | 48.3 | 4.7 |
| 70°-80° | 5.5 | 0.5 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 458.0 | 44.4 |
| 0°-40° | 674.4 | 65.3 |
| 0°-60° | 978.0 | 94.8 |
| 0°-90° | 1032.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1032.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 737 | |
| 5° | 718 | 67 |
| 15° | 608 | 170 |
| 25° | 482 | 221 |
| 35° | 344 | 216 |
| 45° | 239 | 183 |
| 55° | 134 | 120 |
| 65° | 47 | 48 |
| 75° | 2 | 6 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P856728

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBSLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 736.9 |
| 2.5° | 731.2 |
| 5° | 717.5 |
| 7.5° | 694.6 |
| 10° | 666.0 |
| 12.5° | 635.2 |
| 15° | 607.8 |
| 17.5° | 578.1 |
| 20° | 548.4 |
| 22.5° | 516.4 |
| 25° | 482.1 |
| 27.5° | 446.7 |
| 30° | 410.1 |
| 32.5° | 375.9 |
| 35° | 343.9 |
| 37.5° | 317.6 |
| 40° | 289.0 |
| 42.5° | 263.9 |
| 45° | 238.8 |
| 47.5° | 212.5 |
| 50° | 186.2 |
| 52.5° | 160.0 |
| 55° | 133.7 |
| 57.5° | 109.7 |
| 60° | 86.8 |
| 62.5° | 66.3 |
| 65° | 46.8 |
| 67.5° | 30.8 |
| 70° | 18.3 |
| 72.5° | 8.0 |
| 75° | 2.3 |
| 77.5° | 1.1 |
| 80° | 1.1 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)