

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857423

Luminaire Tested: **LX4C25D010 EX4C259050 4LBMH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P857423  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259050 4LBMH  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1950.0 lumens  
Efficiency: N/A  
Efficacy: 61.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857423

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P857423

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																											
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																											
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																											
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																											
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																											
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																											
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																											
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																											
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	154415
5°	155004
10°	155474
15°	155486
20°	154624
25°	151007
30°	141135
35°	122216
40°	95471
45°	68506
50°	44494
55°	26645
60°	15578
65°	10000
70°	6645
75°	5031
80°	3750
85°	0



TEST NUMBER: P857423

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.7	6.1
10°-20°	344.9	17.7
20°-30°	508.9	26.1
30°-40°	502.2	25.8
40°-50°	307.4	15.8
50°-60°	117.8	6.0
60°-70°	36.8	1.9
70°-80°	10.8	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.5	49.9
0°-40°	1475.7	75.7
0°-60°	1900.9	97.5
0°-90°	1950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1950.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1257	
5°	1257	120
15°	1222	345
25°	1114	509
35°	815	502
45°	394	307
55°	124	118
65°	34	37
75°	11	11
85°	0	1
90°	0	



TEST NUMBER: P857423

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1256.9
2.5°	1259.5
5°	1256.9
7.5°	1254.2
10°	1246.3
12.5°	1235.7
15°	1222.5
17.5°	1206.6
20°	1182.7
22.5°	1156.4
25°	1114.0
27.5°	1061.0
30°	994.9
32.5°	912.9
35°	814.9
37.5°	706.5
40°	595.3
42.5°	492.2
45°	394.3
47.5°	306.9
50°	232.8
52.5°	172.0
55°	124.4
57.5°	87.3
60°	63.4
62.5°	47.7
65°	34.4
67.5°	26.5
70°	18.5
72.5°	13.2
75°	10.6
77.5°	5.3
80°	5.3
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)