

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857431

Luminaire Tested: **LX4C25D010 EX4C259050 4LBWLI**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P857431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259050 4LBWLI
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2568.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857431

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P857431

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P857431

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	6.0
10°-20°	485.6	18.9
20°-30°	757.5	29.5
30°-40°	737.1	28.7
40°-50°	368.2	14.3
50°-60°	57.0	2.2
60°-70°	6.9	0.3
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.0	54.4
0°-40°	2134.0	83.1
0°-60°	2559.2	99.7
0°-90°	2568.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2568.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1573	
5°	1594	154
15°	1715	486
25°	1665	758
35°	1197	737
45°	462	368
55°	47	57
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P857431

CATALOG NUMBER: LX4C25D010 EX4C259050 4LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1573.4
2.5°	1579.3
5°	1594.0
7.5°	1617.6
10°	1647.0
12.5°	1685.2
15°	1714.6
17.5°	1738.2
20°	1741.1
22.5°	1720.5
25°	1664.7
27.5°	1582.2
30°	1479.3
32.5°	1350.0
35°	1197.0
37.5°	1029.3
40°	852.9
42.5°	664.7
45°	461.8
47.5°	297.0
50°	179.4
52.5°	97.0
55°	47.1
57.5°	20.6
60°	11.8
62.5°	8.8
65°	5.9
67.5°	5.9
70°	2.9
72.5°	2.9
75°	2.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)