

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856751

Luminaire Tested: **LX4C10D010 EX4C109035 4LBSLI**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856751  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C10D010 EX4C109035 4LBSLI  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1047.0 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856751

CATALOG NUMBER: LX4C10D010 EX4C109035 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856751

CATALOG NUMBER: LX4C10D010 EX4C109035 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91845
5°	89767
10°	84293
15°	78424
20°	72730
25°	66299
30°	59028
35°	52327
40°	47022
45°	42097
50°	36104
55°	29044
60°	21647
65°	13808
70°	6645
75°	1092
80°	849
85°	0



TEST NUMBER: P856751

CATALOG NUMBER: LX4C10D010 EX4C109035 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.8	6.5
10°-20°	172.9	16.5
20°-30°	224.0	21.4
30°-40°	219.5	21.0
40°-50°	186.1	17.8
50°-60°	122.0	11.7
60°-70°	49.0	4.7
70°-80°	5.6	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.7	44.4
0°-40°	684.2	65.3
0°-60°	992.2	94.8
0°-90°	1047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	748	
5°	728	68
15°	617	173
25°	489	224
35°	349	219
45°	242	186
55°	136	122
65°	48	49
75°	2	6
85°	0	0
90°	0	



TEST NUMBER: P856751

CATALOG NUMBER: LX4C10D010 EX4C109035 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	747.6
2.5°	741.8
5°	727.9
7.5°	704.7
10°	675.7
12.5°	644.4
15°	616.6
17.5°	586.5
20°	556.3
22.5°	523.9
25°	489.1
27.5°	453.2
30°	416.1
32.5°	381.3
35°	348.9
37.5°	322.2
40°	293.2
42.5°	267.7
45°	242.3
47.5°	215.6
50°	188.9
52.5°	162.3
55°	135.6
57.5°	111.3
60°	88.1
62.5°	67.2
65°	47.5
67.5°	31.3
70°	18.5
72.5°	8.1
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)