

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857447

Luminaire Tested: **LX4C25D010 EX4C259827 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P857447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259827 4LBSLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2199.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857447

CATALOG NUMBER: LX4C25D010 EX4C259827 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P857447

CATALOG NUMBER: LX4C25D010 EX4C259827 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192905
5°	188536
10°	177043
15°	164720
20°	152767
25°	139268
30°	123985
35°	109888
40°	98774
45°	88399
50°	75839
55°	61001
60°	45456
65°	29011
70°	14009
75°	2326
80°	1698
85°	0



TEST NUMBER: P857447

CATALOG NUMBER: LX4C25D010 EX4C259827 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.4	6.5
10°-20°	363.1	16.5
20°-30°	470.5	21.4
30°-40°	461.0	21.0
40°-50°	390.8	17.8
50°-60°	256.2	11.6
60°-70°	103.0	4.7
70°-80°	11.8	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	976.0	44.4
0°-40°	1437.0	65.3
0°-60°	2084.0	94.8
0°-90°	2199.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2199.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1570	
5°	1529	142
15°	1295	363
25°	1027	471
35°	733	461
45°	509	391
55°	285	256
65°	100	103
75°	5	12
85°	0	0
90°	0	



TEST NUMBER: P857447

CATALOG NUMBER: LX4C25D010 EX4C259827 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1570.2
2.5°	1558.0
5°	1528.8
7.5°	1480.1
10°	1419.2
12.5°	1353.5
15°	1295.1
17.5°	1231.9
20°	1168.5
22.5°	1100.4
25°	1027.4
27.5°	951.8
30°	874.0
32.5°	801.0
35°	732.7
37.5°	676.7
40°	615.9
42.5°	562.3
45°	508.8
47.5°	452.8
50°	396.8
52.5°	340.8
55°	284.8
57.5°	233.7
60°	185.0
62.5°	141.2
65°	99.8
67.5°	65.7
70°	39.0
72.5°	17.0
75°	4.9
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)