

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857455

Luminaire Tested: **LX4C25D010 EX4C259830 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259830 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1678.2 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857455

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857455

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132903
5°	133411
10°	133805
15°	133814
20°	133078
25°	129955
30°	121474
35°	105193
40°	82176
45°	58950
50°	38302
55°	22918
60°	13416
65°	8605
70°	5747
75°	4319
80°	3184
85°	0



TEST NUMBER: P857455

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	6.1
10°-20°	296.8	17.7
20°-30°	438.0	26.1
30°-40°	432.2	25.8
40°-50°	264.5	15.8
50°-60°	101.4	6.0
60°-70°	31.7	1.9
70°-80°	9.3	0.6
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.8	49.9
0°-40°	1270.1	75.7
0°-60°	1636.0	97.5
0°-90°	1678.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1678.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1082	
5°	1082	103
15°	1052	297
25°	959	438
35°	701	432
45°	339	265
55°	107	101
65°	30	32
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P857455

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1081.8
2.5°	1084.0
5°	1081.8
7.5°	1079.5
10°	1072.6
12.5°	1063.5
15°	1052.1
17.5°	1038.4
20°	1017.9
22.5°	995.2
25°	958.7
27.5°	913.1
30°	856.3
32.5°	785.7
35°	701.4
37.5°	608.0
40°	512.4
42.5°	423.6
45°	339.3
47.5°	264.1
50°	200.4
52.5°	148.0
55°	107.0
57.5°	75.1
60°	54.6
62.5°	41.0
65°	29.6
67.5°	22.8
70°	16.0
72.5°	11.4
75°	9.1
77.5°	4.5
80°	4.5
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)