

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856828

Luminaire Tested: **LX4C10D010 EX4C109830 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P856828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109830 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 882.8 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856828

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P856828

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56721
5°	56457
10°	55301
15°	53279
20°	50831
25°	48094
30°	45366
35°	42713
40°	40222
45°	37493
50°	34192
55°	30201
60°	25554
65°	20058
70°	14332
75°	7832
80°	1415
85°	0



TEST NUMBER: P856828

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	4.9
10°-20°	117.5	13.3
20°-30°	163.2	18.5
30°-40°	178.1	20.2
40°-50°	166.2	18.8
50°-60°	126.1	14.3
60°-70°	69.0	7.8
70°-80°	19.0	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.0	36.7
0°-40°	502.2	56.9
0°-60°	794.5	90.0
0°-90°	882.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	882.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	462	
5°	458	43
15°	419	118
25°	355	163
35°	285	178
45°	216	166
55°	141	126
65°	69	69
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P856828

CATALOG NUMBER: LX4C10D010 EX4C109830 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	461.7
2.5°	461.7
5°	457.8
7.5°	452.0
10°	443.3
12.5°	431.6
15°	418.9
17.5°	403.4
20°	388.8
22.5°	371.3
25°	354.8
27.5°	338.2
30°	319.8
32.5°	302.3
35°	284.8
37.5°	267.3
40°	250.8
42.5°	233.3
45°	215.8
47.5°	198.3
50°	178.9
52.5°	160.3
55°	141.0
57.5°	122.4
60°	104.0
62.5°	85.5
65°	69.0
67.5°	53.4
70°	39.9
72.5°	27.2
75°	16.5
77.5°	7.8
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)