

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857463

Luminaire Tested: **LX4C25D010 EX4C259830 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857463  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259830 4LBWLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2209.8 lumens  
Efficiency: N/A  
Efficacy: 70.2 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857463  
CATALOG NUMBER: LX4C25D010 EX4C259830 4LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P857463

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  | 92  | 92  | 92  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  | 93  | 90  | 88  | 90  | 88  | 86  | 84  | 84  | 84  | 84  |
| 3   | 100 | 93  | 87  | 83  | 98  | 92  | 86  | 82  | 89  | 85  | 81  | 86  | 83  | 80  | 84  | 81  | 78  | 77  | 77  | 77  | 77  |
| 4   | 94  | 86  | 79  | 75  | 92  | 84  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  | 70  | 70  | 70  |
| 5   | 88  | 79  | 72  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  | 74  | 70  | 66  | 73  | 69  | 65  | 64  | 64  | 64  | 64  |
| 6   | 83  | 73  | 66  | 62  | 82  | 72  | 66  | 61  | 71  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 58  | 58  | 58  | 58  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  | 64  | 59  | 55  | 63  | 59  | 55  | 54  | 54  | 54  | 54  |
| 8   | 74  | 63  | 56  | 52  | 72  | 62  | 56  | 51  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 49  | 49  | 49  | 49  |
| 9   | 69  | 59  | 52  | 48  | 68  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 45  | 45  | 45  | 45  |
| 10  | 66  | 55  | 48  | 44  | 65  | 54  | 48  | 44  | 53  | 48  | 44  | 53  | 47  | 44  | 52  | 47  | 43  | 42  | 42  | 42  | 42  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P857463

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBWLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 132.4  | 6.0       |
| 10°-20°   | 417.8  | 18.9      |
| 20°-30°   | 651.8  | 29.5      |
| 30°-40°   | 634.3  | 28.7      |
| 40°-50°   | 316.8  | 14.3      |
| 50°-60°   | 49.1   | 2.2       |
| 60°-70°   | 6.0    | 0.3       |
| 70°-80°   | 1.6    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1202.1 | 54.4      |
| 0°-40°    | 1836.3 | 83.1      |
| 0°-60°    | 2202.2 | 99.7      |
| 0°-90°    | 2209.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2209.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1354 |      |
| 5°  | 1372 | 132  |
| 15° | 1475 | 418  |
| 25° | 1432 | 652  |
| 35° | 1030 | 634  |
| 45° | 397  | 317  |
| 55° | 41   | 49   |
| 65° | 5    | 6    |
| 75° | 2    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P857463

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1353.9 |
| 2.5°  | 1358.9 |
| 5°    | 1371.6 |
| 7.5°  | 1391.9 |
| 10°   | 1417.2 |
| 12.5° | 1450.1 |
| 15°   | 1475.4 |
| 17.5° | 1495.7 |
| 20°   | 1498.2 |
| 22.5° | 1480.5 |
| 25°   | 1432.4 |
| 27.5° | 1361.5 |
| 30°   | 1273.0 |
| 32.5° | 1161.7 |
| 35°   | 1030.1 |
| 37.5° | 885.7  |
| 40°   | 733.9  |
| 42.5° | 572.0  |
| 45°   | 397.4  |
| 47.5° | 255.6  |
| 50°   | 154.4  |
| 52.5° | 83.5   |
| 55°   | 40.6   |
| 57.5° | 17.7   |
| 60°   | 10.2   |
| 62.5° | 7.6    |
| 65°   | 5.1    |
| 67.5° | 5.1    |
| 70°   | 2.5    |
| 72.5° | 2.5    |
| 75°   | 2.5    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)