

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856844

Luminaire Tested: **LX4C10D010 EX4C109835 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P856844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109835 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 761.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856844

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P856844

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60309
5°	60539
10°	60715
15°	60719
20°	60388
25°	58979
30°	55112
35°	47737
40°	37287
45°	26756
50°	17392
55°	10410
60°	6094
65°	3924
70°	2586
75°	1946
80°	1486
85°	0



TEST NUMBER: P856844

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	6.1
10°-20°	134.7	17.7
20°-30°	198.8	26.1
30°-40°	196.1	25.8
40°-50°	120.0	15.8
50°-60°	46.0	6.0
60°-70°	14.4	1.9
70°-80°	4.2	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.2	49.9
0°-40°	576.3	75.7
0°-60°	742.4	97.5
0°-90°	761.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	491	
5°	491	47
15°	477	135
25°	435	199
35°	318	196
45°	154	120
55°	49	46
65°	14	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P856844

CATALOG NUMBER: LX4C10D010 EX4C109835 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	490.9
2.5°	491.9
5°	490.9
7.5°	489.8
10°	486.7
12.5°	482.6
15°	477.4
17.5°	471.2
20°	461.9
22.5°	451.6
25°	435.1
27.5°	414.4
30°	388.5
32.5°	356.5
35°	318.3
37.5°	275.9
40°	232.5
42.5°	192.2
45°	154.0
47.5°	119.9
50°	91.0
52.5°	67.1
55°	48.6
57.5°	34.1
60°	24.8
62.5°	18.6
65°	13.5
67.5°	10.3
70°	7.2
72.5°	5.2
75°	4.1
77.5°	2.1
80°	2.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)