

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857488

Luminaire Tested: **LX4C25D010 EX4C259840 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259840 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1894.1 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857488

CATALOG NUMBER: LX4C25D010 EX4C259840 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857488

CATALOG NUMBER: LX4C25D010 EX4C259840 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149980
5°	150552
10°	151008
15°	151022
20°	150192
25°	146669
30°	137093
35°	118706
40°	92744
45°	66543
50°	43214
55°	25874
60°	15136
65°	9709
70°	6466
75°	4889
80°	3679
85°	0



TEST NUMBER: P857488

CATALOG NUMBER: LX4C25D010 EX4C259840 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	6.1
10°-20°	335.0	17.7
20°-30°	494.3	26.1
30°-40°	487.8	25.8
40°-50°	298.5	15.8
50°-60°	114.4	6.0
60°-70°	35.8	1.9
70°-80°	10.5	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.6	49.9
0°-40°	1433.4	75.7
0°-60°	1846.4	97.5
0°-90°	1894.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1894.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1221	
5°	1221	116
15°	1187	335
25°	1082	494
35°	792	488
45°	383	299
55°	121	114
65°	33	36
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P857488

CATALOG NUMBER: LX4C25D010 EX4C259840 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1220.8
2.5°	1223.4
5°	1220.8
7.5°	1218.3
10°	1210.5
12.5°	1200.3
15°	1187.4
17.5°	1171.9
20°	1148.8
22.5°	1123.1
25°	1082.0
27.5°	1030.6
30°	966.4
32.5°	886.7
35°	791.5
37.5°	686.2
40°	578.3
42.5°	478.1
45°	383.0
47.5°	298.1
50°	226.1
52.5°	167.1
55°	120.8
57.5°	84.8
60°	61.6
62.5°	46.3
65°	33.4
67.5°	25.7
70°	18.0
72.5°	12.8
75°	10.3
77.5°	5.2
80°	5.2
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)