

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856851

Luminaire Tested: **LX4C10D010 EX4C109840 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P856851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109840 4LBMLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 856.1 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856851

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P856851

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73			
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63			
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270646
5°	243550
10°	188820
15°	136663
20°	94628
25°	68983
30°	50119
35°	29665
40°	12477
45°	3892
50°	516
55°	278
60°	319
65°	378
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856851

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.6	20.3
10°-20°	297.2	34.7
20°-30°	236.2	27.6
30°-40°	125.1	14.6
40°-50°	21.6	2.5
50°-60°	1.6	0.2
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.1	82.6
0°-40°	832.1	97.2
0°-60°	855.3	99.9
0°-90°	856.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	856.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2203	
5°	1975	174
15°	1074	297
25°	509	236
35°	198	125
45°	22	22
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856851

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2203.0
2.5°	2146.3
5°	1974.9
7.5°	1750.8
10°	1513.6
12.5°	1284.1
15°	1074.5
17.5°	879.3
20°	723.8
22.5°	605.1
25°	508.9
27.5°	431.2
30°	353.3
32.5°	274.2
35°	197.8
37.5°	130.6
40°	77.8
42.5°	44.9
45°	22.4
47.5°	7.9
50°	2.7
52.5°	2.7
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)