

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856858

Luminaire Tested: **LX4C10D010 EX4C109840 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P856858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C10D010 EX4C109840 4LBWLI
Description:
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 903.4 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856858
CATALOG NUMBER: LX4C10D010 EX4C109840 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856858

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P856858

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	6.0
10°-20°	170.8	18.9
20°-30°	266.5	29.5
30°-40°	259.3	28.7
40°-50°	129.5	14.3
50°-60°	20.1	2.2
60°-70°	2.4	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.4	54.4
0°-40°	750.7	83.1
0°-60°	900.2	99.7
0°-90°	903.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	903.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	561	54
15°	603	171
25°	586	266
35°	421	259
45°	162	130
55°	17	20
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P856858

CATALOG NUMBER: LX4C10D010 EX4C109840 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	553.5
2.5°	555.6
5°	560.7
7.5°	569.0
10°	579.4
12.5°	592.7
15°	603.2
17.5°	611.5
20°	612.4
22.5°	605.2
25°	585.6
27.5°	556.5
30°	520.3
32.5°	474.9
35°	421.1
37.5°	362.0
40°	300.0
42.5°	233.8
45°	162.5
47.5°	104.5
50°	63.1
52.5°	34.2
55°	16.6
57.5°	7.2
60°	4.1
62.5°	3.1
65°	2.1
67.5°	2.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)