

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857499

Luminaire Tested: **LX4C25D010 EX4C259850 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P857499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259850 4LBSLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2369.3 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857499

CATALOG NUMBER: LX4C25D010 EX4C259850 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P857499

CATALOG NUMBER: LX4C25D010 EX4C259850 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207844
5°	203137
10°	190766
15°	177477
20°	164612
25°	150045
30°	133589
35°	118406
40°	106408
45°	95245
50°	81706
55°	65713
60°	48969
65°	31250
70°	15050
75°	2516
80°	1839
85°	0



TEST NUMBER: P857499

CATALOG NUMBER: LX4C25D010 EX4C259850 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	6.5
10°-20°	391.2	16.5
20°-30°	507.0	21.4
30°-40°	496.7	21.0
40°-50°	421.0	17.8
50°-60°	276.0	11.6
60°-70°	110.9	4.7
70°-80°	12.7	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1051.6	44.4
0°-40°	1548.4	65.4
0°-60°	2245.4	94.8
0°-90°	2369.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2369.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1692	
5°	1647	153
15°	1395	391
25°	1107	507
35°	790	497
45°	548	421
55°	307	276
65°	108	111
75°	5	13
85°	0	0
90°	0	



TEST NUMBER: P857499

CATALOG NUMBER: LX4C25D010 EX4C259850 4LBSLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1691.8
2.5°	1678.7
5°	1647.2
7.5°	1594.7
10°	1529.2
12.5°	1458.4
15°	1395.4
17.5°	1327.3
20°	1259.1
22.5°	1185.6
25°	1106.9
27.5°	1025.6
30°	941.7
32.5°	862.9
35°	789.5
37.5°	729.2
40°	663.5
42.5°	605.9
45°	548.2
47.5°	487.9
50°	427.5
52.5°	367.2
55°	306.8
57.5°	251.8
60°	199.3
62.5°	152.1
65°	107.5
67.5°	70.8
70°	41.9
72.5°	18.4
75°	5.3
77.5°	2.6
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)