

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856864

Luminaire Tested: **LX4C10D010 EX4C109850 4LBMLI**

Issue Date: 1/26/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856864  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/26/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C10D010 EX4C109850 4LBMLI  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 873.8 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856864

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856864

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	276297
5°	248631
10°	192737
15°	139499
20°	96602
25°	70420
30°	51169
35°	30280
40°	12734
45°	3961
50°	516
55°	278
60°	319
65°	378
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856864

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.2	20.3
10°-20°	303.4	34.7
20°-30°	241.1	27.6
30°-40°	127.6	14.6
40°-50°	22.0	2.5
50°-60°	1.6	0.2
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.8	82.6
0°-40°	849.4	97.2
0°-60°	873.0	99.9
0°-90°	873.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2249	
5°	2016	177
15°	1097	303
25°	520	241
35°	202	128
45°	23	22
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856864

CATALOG NUMBER: LX4C10D010 EX4C109850 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2249.0
2.5°	2191.0
5°	2016.1
7.5°	1787.3
10°	1545.0
12.5°	1310.9
15°	1096.8
17.5°	897.7
20°	738.9
22.5°	617.7
25°	519.5
27.5°	440.1
30°	360.7
32.5°	279.9
35°	201.9
37.5°	133.2
40°	79.4
42.5°	45.7
45°	22.8
47.5°	8.1
50°	2.7
52.5°	2.7
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)