

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856890

Luminaire Tested: **LX4C10D010 EX4C109030 4LBMLI**

Issue Date: 1/26/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P856890  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/26/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C10D010 EX4C109030 4LBMLI  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1299.1 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856890

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856890

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	410711
5°	369586
10°	286510
15°	207392
20°	143589
25°	104688
30°	76079
35°	45008
40°	18940
45°	5890
50°	765
55°	428
60°	491
65°	581
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856890

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	263.5	20.3
10°-20°	451.0	34.7
20°-30°	358.5	27.6
30°-40°	189.8	14.6
40°-50°	32.7	2.5
50°-60°	2.4	0.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.9	82.6
0°-40°	1262.7	97.2
0°-60°	1297.8	99.9
0°-90°	1299.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3343	
5°	2997	263
15°	1631	451
25°	772	358
35°	300	190
45°	34	33
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856890

CATALOG NUMBER: LX4C10D010 EX4C109030 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3343.1
2.5°	3257.0
5°	2996.9
7.5°	2656.9
10°	2296.7
12.5°	1948.5
15°	1630.6
17.5°	1334.4
20°	1098.3
22.5°	918.2
25°	772.3
27.5°	654.2
30°	536.3
32.5°	416.0
35°	300.1
37.5°	198.2
40°	118.1
42.5°	67.9
45°	33.9
47.5°	12.1
50°	4.0
52.5°	4.0
55°	2.0
57.5°	2.0
60°	2.0
62.5°	2.0
65°	2.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)