

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858132

Luminaire Tested: **LX4C45D010 EX4C459030 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P858132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459030 4LBNLI
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3430.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858132

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P858132

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			90																
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85																
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81																
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			77																
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73			73																
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69			69																
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			66																
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63			63																
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61			61																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1084415
5°	975853
10°	756501
15°	547554
20°	379140
25°	276394
30°	200830
35°	118841
40°	49989
45°	15585
50°	2026
55°	1135
60°	1302
65°	1541
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858132

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.6	20.3
10°-20°	1190.9	34.7
20°-30°	946.5	27.6
30°-40°	501.0	14.6
40°-50°	86.3	2.5
50°-60°	6.5	0.2
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2833.0	82.6
0°-40°	3334.0	97.2
0°-60°	3426.8	99.9
0°-90°	3430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3430.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8827	
5°	7913	696
15°	4305	1191
25°	2039	946
35°	792	501
45°	90	86
55°	5	6
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858132

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8826.9
2.5°	8599.6
5°	7913.0
7.5°	7015.1
10°	6064.2
12.5°	5145.1
15°	4305.1
17.5°	3523.3
20°	2900.0
22.5°	2424.5
25°	2039.0
27.5°	1727.4
30°	1415.7
32.5°	1098.8
35°	792.4
37.5°	523.0
40°	311.7
42.5°	179.6
45°	89.7
47.5°	31.7
50°	10.6
52.5°	10.6
55°	5.3
57.5°	5.3
60°	5.3
62.5°	5.3
65°	5.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)