

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857171

Luminaire Tested: **LX4C20D010 EX4C209035 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857171  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C20D010 EX4C209035 4LSH  
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LSB TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1984.0 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857171

CATALOG NUMBER: LX4C20D010 EX4C209035 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P857171

CATALOG NUMBER: LX4C20D010 EX4C209035 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	127473
5°	126887
10°	124262
15°	119747
20°	114239
25°	108077
30°	101954
35°	95985
40°	90387
45°	84247
50°	76833
55°	67855
60°	57422
65°	45087
70°	32184
75°	17610
80°	3113
85°	0



TEST NUMBER: P857171

CATALOG NUMBER: LX4C20D010 EX4C209035 4LSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.2	4.9
10°-20°	264.2	13.3
20°-30°	366.9	18.5
30°-40°	400.3	20.2
40°-50°	373.5	18.8
50°-60°	283.5	14.3
60°-70°	155.2	7.8
70°-80°	42.7	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.2	36.7
0°-40°	1128.6	56.9
0°-60°	1785.5	90.0
0°-90°	1984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1984.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1038	
5°	1029	97
15°	942	264
25°	797	367
35°	640	400
45°	485	373
55°	317	283
65°	155	155
75°	37	43
85°	0	1
90°	0	



TEST NUMBER: P857171

CATALOG NUMBER: LX4C20D010 EX4C209035 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1037.6
2.5°	1037.6
5°	1028.9
7.5°	1015.8
10°	996.1
12.5°	969.9
15°	941.5
17.5°	906.6
20°	873.8
22.5°	834.5
25°	797.3
27.5°	760.2
30°	718.7
32.5°	679.4
35°	640.0
37.5°	600.7
40°	563.6
42.5°	524.3
45°	484.9
47.5°	445.6
50°	402.0
52.5°	360.4
55°	316.8
57.5°	275.2
60°	233.7
62.5°	192.3
65°	155.1
67.5°	120.1
70°	89.6
72.5°	61.2
75°	37.1
77.5°	17.5
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)