

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857215

Luminaire Tested: **LX4C20D010 EX4C209050 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857215  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C20D010 EX4C209050 4LBSH  
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2028.0 lumens  
Efficiency: N/A  
Efficacy: 93.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857215

CATALOG NUMBER: LX4C20D010 EX4C209050 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P857215

CATALOG NUMBER: LX4C20D010 EX4C209050 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130298
5°	129699
10°	127019
15°	122405
20°	116775
25°	110476
30°	104210
35°	98115
40°	92391
45°	86123
50°	78534
55°	69354
60°	58699
65°	46075
70°	32903
75°	18037
80°	3184
85°	0



TEST NUMBER: P857215

CATALOG NUMBER: LX4C20D010 EX4C209050 4LSBH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.3	4.9
10°-20°	270.0	13.3
20°-30°	375.0	18.5
30°-40°	409.2	20.2
40°-50°	381.7	18.8
50°-60°	289.7	14.3
60°-70°	158.6	7.8
70°-80°	43.7	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.4	36.7
0°-40°	1153.6	56.9
0°-60°	1825.1	90.0
0°-90°	2028.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2028.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1061	
5°	1052	99
15°	962	270
25°	815	375
35°	654	409
45°	496	382
55°	324	290
65°	158	159
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P857215

CATALOG NUMBER: LX4C20D010 EX4C209050 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1060.6
2.5°	1060.6
5°	1051.7
7.5°	1038.3
10°	1018.2
12.5°	991.4
15°	962.4
17.5°	926.7
20°	893.2
22.5°	853.0
25°	815.0
27.5°	777.1
30°	734.6
32.5°	694.4
35°	654.2
37.5°	614.0
40°	576.1
42.5°	535.9
45°	495.7
47.5°	455.5
50°	410.9
52.5°	368.4
55°	323.8
57.5°	281.3
60°	238.9
62.5°	196.5
65°	158.5
67.5°	122.8
70°	91.6
72.5°	62.5
75°	38.0
77.5°	17.9
80°	4.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)