

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857229

Luminaire Tested: **LX4C20D010 EX4C209827 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209827 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1411.7 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857229

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P857229

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227783
5°	235534
10°	237933
15°	214323
20°	178117
25°	139742
30°	102266
35°	52837
40°	25099
45°	8826
50°	1988
55°	1307
60°	909
65°	669
70°	467
75°	332
80°	283
85°	0



TEST NUMBER: P857229

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	12.9
10°-20°	464.1	32.9
20°-30°	469.7	33.3
30°-40°	239.4	17.0
40°-50°	46.9	3.3
50°-60°	5.7	0.4
60°-70°	2.3	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.2	79.1
0°-40°	1355.7	96.0
0°-60°	1408.3	99.8
0°-90°	1411.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1411.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1854	
5°	1910	182
15°	1685	464
25°	1031	470
35°	352	239
45°	51	47
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P857229

CATALOG NUMBER: LX4C20D010 EX4C209827 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1854.1
2.5°	1871.2
5°	1909.9
7.5°	1932.1
10°	1907.3
12.5°	1823.4
15°	1685.1
17.5°	1521.9
20°	1362.4
22.5°	1197.1
25°	1030.9
27.5°	865.3
30°	720.9
32.5°	543.2
35°	352.3
37.5°	236.0
40°	156.5
42.5°	98.3
45°	50.8
47.5°	18.2
50°	10.4
52.5°	7.8
55°	6.1
57.5°	4.7
60°	3.7
62.5°	3.0
65°	2.3
67.5°	1.7
70°	1.3
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)