

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857269

Luminaire Tested: **LX4C20D010 EX4C209840 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209840 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1356.4 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857269

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857269

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107411
5°	107821
10°	108145
15°	108147
20°	107545
25°	105027
30°	98166
35°	85007
40°	66411
45°	47640
50°	30943
55°	18527
60°	10836
65°	6977
70°	4634
75°	3513
80°	2618
85°	0



TEST NUMBER: P857269

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.3	6.1
10°-20°	239.9	17.7
20°-30°	354.0	26.1
30°-40°	349.3	25.8
40°-50°	213.8	15.8
50°-60°	82.0	6.0
60°-70°	25.7	1.9
70°-80°	7.5	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.1	49.9
0°-40°	1026.4	75.7
0°-60°	1322.2	97.5
0°-90°	1356.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	874	83
15°	850	240
25°	775	354
35°	567	349
45°	274	214
55°	86	82
65°	24	26
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P857269

CATALOG NUMBER: LX4C20D010 EX4C209840 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	874.3
2.5°	876.0
5°	874.3
7.5°	872.4
10°	866.9
12.5°	859.5
15°	850.3
17.5°	839.2
20°	822.6
22.5°	804.4
25°	774.8
27.5°	738.0
30°	692.0
32.5°	635.0
35°	566.8
37.5°	491.3
40°	414.1
42.5°	342.3
45°	274.2
47.5°	213.5
50°	161.9
52.5°	119.7
55°	86.5
57.5°	60.7
60°	44.1
62.5°	33.2
65°	24.0
67.5°	18.5
70°	12.9
72.5°	9.2
75°	7.4
77.5°	3.7
80°	3.7
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)