

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858211

Luminaire Tested: **LX4C45D010 EX4C459827 4LBMLI**

Issue Date: 1/26/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858211  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/26/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C45D010 EX4C459827 4LBMLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3748.9 lumens  
Efficiency: N/A  
Efficacy: 75.6 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858211

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P858211

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90																											
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																											
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81																											
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77																											
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73																											
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69																											
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																											
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63																											
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1185229
5°	1066569
10°	826834
15°	598467
20°	414387
25°	302095
30°	219513
35°	129895
40°	54623
45°	17027
50°	2217
55°	1242
60°	1425
65°	1686
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858211

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	760.3	20.3
10°-20°	1301.6	34.7
20°-30°	1034.5	27.6
30°-40°	547.6	14.6
40°-50°	94.3	2.5
50°-60°	7.1	0.2
60°-70°	3.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3096.3	82.6
0°-40°	3644.0	97.2
0°-60°	3745.4	99.9
0°-90°	3748.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3748.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9648	
5°	8649	760
15°	4705	1302
25°	2229	1034
35°	866	548
45°	98	94
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858211

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9647.5
2.5°	9399.0
5°	8648.6
7.5°	7667.3
10°	6628.0
12.5°	5623.4
15°	4705.4
17.5°	3850.8
20°	3169.6
22.5°	2649.9
25°	2228.6
27.5°	1888.0
30°	1547.4
32.5°	1200.9
35°	866.1
37.5°	571.7
40°	340.6
42.5°	196.4
45°	98.0
47.5°	34.7
50°	11.6
52.5°	11.6
55°	5.8
57.5°	5.8
60°	5.8
62.5°	5.8
65°	5.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)