

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858212

Luminaire Tested: **LX4C45D010 EX4C459827 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459827 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2496.9 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858212

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858212

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	385133
5°	376566
10°	348174
15°	312423
20°	275007
25°	236677
30°	190602
35°	126880
40°	65994
45°	29866
50°	12977
55°	8717
60°	5578
65°	3953
70°	3269
75°	2136
80°	0
85°	0



TEST NUMBER: P858212

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.8	11.3
10°-20°	686.1	27.5
20°-30°	796.5	31.9
30°-40°	527.5	21.1
40°-50°	148.0	5.9
50°-60°	37.2	1.5
60°-70°	14.0	0.6
70°-80°	4.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1765.5	70.7
0°-40°	2293.0	91.8
0°-60°	2478.1	99.3
0°-90°	2496.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2496.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3135	
5°	3054	283
15°	2456	686
25°	1746	797
35°	846	528
45°	172	148
55°	41	37
65°	14	14
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P858212

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3134.9
2.5°	3121.4
5°	3053.5
7.5°	2935.8
10°	2791.0
12.5°	2628.1
15°	2456.4
17.5°	2288.9
20°	2103.5
22.5°	1931.6
25°	1746.0
27.5°	1569.7
30°	1343.6
32.5°	1103.7
35°	846.0
37.5°	606.2
40°	411.5
42.5°	266.8
45°	171.9
47.5°	104.2
50°	67.9
52.5°	49.7
55°	40.7
57.5°	31.7
60°	22.7
62.5°	18.1
65°	13.6
67.5°	9.1
70°	9.1
72.5°	4.5
75°	4.5
77.5°	4.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)