

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857285

Luminaire Tested: **LX4C20D010 EX4C209850 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P857285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C20D010 EX4C209850 4LBNLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1355.5 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857285

CATALOG NUMBER: LX4C20D010 EX4C209850 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P857285

CATALOG NUMBER: LX4C20D010 EX4C209850 4LBNI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73			
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63			
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	428525
5°	385630
10°	298948
15°	216384
20°	149826
25°	109229
30°	79370
35°	46958
40°	19742
45°	6168
50°	803
55°	450
60°	516
65°	610
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857285

CATALOG NUMBER: LX4C20D010 EX4C209850 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.9	20.3
10°-20°	470.6	34.7
20°-30°	374.0	27.6
30°-40°	198.0	14.6
40°-50°	34.1	2.5
50°-60°	2.6	0.2
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1119.5	82.6
0°-40°	1317.5	97.2
0°-60°	1354.2	99.9
0°-90°	1355.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3488	
5°	3127	275
15°	1701	471
25°	806	374
35°	313	198
45°	36	34
55°	2	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857285

CATALOG NUMBER: LX4C20D010 EX4C209850 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3488.1
2.5°	3398.3
5°	3127.0
7.5°	2772.2
10°	2396.4
12.5°	2033.2
15°	1701.3
17.5°	1392.3
20°	1146.0
22.5°	958.1
25°	805.8
27.5°	682.6
30°	559.5
32.5°	434.2
35°	313.1
37.5°	206.7
40°	123.1
42.5°	71.0
45°	35.5
47.5°	12.6
50°	4.2
52.5°	4.2
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	2.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)