

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858215

Luminaire Tested: **LX4C45D010 EX4C459827 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P858215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459827 4LBSLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4094.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858215

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P858215

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359125
5°	351001
10°	329611
15°	306661
20°	284407
25°	259260
30°	230819
35°	204598
40°	183885
45°	164585
50°	141185
55°	113563
60°	84621
65°	54011
70°	26042
75°	4319
80°	3184
85°	0



TEST NUMBER: P858215

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.1	6.5
10°-20°	676.0	16.5
20°-30°	876.0	21.4
30°-40°	858.3	21.0
40°-50°	727.5	17.8
50°-60°	476.9	11.6
60°-70°	191.7	4.7
70°-80°	21.9	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.1	44.4
0°-40°	2675.4	65.3
0°-60°	3879.8	94.8
0°-90°	4094.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4094.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2923	
5°	2846	265
15°	2411	676
25°	1913	876
35°	1364	858
45°	947	728
55°	530	477
65°	186	192
75°	9	22
85°	0	1
90°	0	



TEST NUMBER: P858215

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2923.2
2.5°	2900.6
5°	2846.2
7.5°	2755.5
10°	2642.2
12.5°	2519.9
15°	2411.1
17.5°	2293.3
20°	2175.4
22.5°	2048.6
25°	1912.6
27.5°	1772.1
30°	1627.1
32.5°	1491.1
35°	1364.2
37.5°	1259.9
40°	1146.6
42.5°	1046.9
45°	947.3
47.5°	843.0
50°	738.7
52.5°	634.6
55°	530.2
57.5°	435.1
60°	344.4
62.5°	262.8
65°	185.8
67.5°	122.3
70°	72.5
72.5°	31.7
75°	9.1
77.5°	4.5
80°	4.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)