

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858231

Luminaire Tested: **LX4C45D010 EX4C459830 4LBWLI**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P858231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459830 4LBWLI
Description:
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4113.6 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858231
CATALOG NUMBER: LX4C45D010 EX4C459830 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P858231

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P858231

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.5	6.0
10°-20°	777.8	18.9
20°-30°	1213.4	29.5
30°-40°	1180.7	28.7
40°-50°	589.7	14.3
50°-60°	91.3	2.2
60°-70°	11.1	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2237.8	54.4
0°-40°	3418.4	83.1
0°-60°	4099.4	99.7
0°-90°	4113.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4113.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2520	
5°	2553	246
15°	2747	778
25°	2667	1213
35°	1917	1181
45°	740	590
55°	75	91
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P858231

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2520.4
2.5°	2529.8
5°	2553.4
7.5°	2591.1
10°	2638.3
12.5°	2699.4
15°	2746.6
17.5°	2784.3
20°	2789.0
22.5°	2756.0
25°	2666.6
27.5°	2534.5
30°	2369.6
32.5°	2162.6
35°	1917.4
37.5°	1648.8
40°	1366.2
42.5°	1064.7
45°	739.7
47.5°	475.7
50°	287.3
52.5°	155.4
55°	75.4
57.5°	33.0
60°	18.9
62.5°	14.2
65°	9.5
67.5°	9.5
70°	4.7
72.5°	4.7
75°	4.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)