

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858238

Luminaire Tested: **LX4C45D010 EX4C459835 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459835 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2632.4 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858238

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858238

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	406055
5°	397013
10°	367073
15°	329377
20°	289951
25°	249527
30°	200929
35°	133764
40°	69586
45°	31499
50°	13666
55°	9167
60°	5872
65°	4186
70°	3412
75°	2278
80°	0
85°	0



TEST NUMBER: P858238

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.2	11.3
10°-20°	723.3	27.5
20°-30°	839.8	31.9
30°-40°	556.1	21.1
40°-50°	156.0	5.9
50°-60°	39.1	1.5
60°-70°	14.7	0.6
70°-80°	5.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1861.3	70.7
0°-40°	2417.5	91.8
0°-60°	2612.6	99.2
0°-90°	2632.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2632.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3305	
5°	3219	298
15°	2590	723
25°	1841	840
35°	892	556
45°	181	156
55°	43	39
65°	14	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P858238

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3305.2
2.5°	3290.8
5°	3219.3
7.5°	3095.1
10°	2942.5
12.5°	2770.8
15°	2589.7
17.5°	2413.2
20°	2217.8
22.5°	2036.5
25°	1840.8
27.5°	1655.0
30°	1416.4
32.5°	1163.6
35°	891.9
37.5°	639.1
40°	433.9
42.5°	281.3
45°	181.3
47.5°	109.8
50°	71.5
52.5°	52.3
55°	42.8
57.5°	33.4
60°	23.9
62.5°	19.2
65°	14.4
67.5°	9.5
70°	9.5
72.5°	4.8
75°	4.8
77.5°	4.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)