

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857312

Luminaire Tested: **LX4C20D010 EX4C209030 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857312  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C20D010 EX4C209030 4LBSH  
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2309.1 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 32.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857312

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P857312

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	148370
5°	147679
10°	144634
15°	139372
20°	132960
25°	125794
30°	118651
35°	111717
40°	105189
45°	98042
50°	89409
55°	78971
60°	66857
65°	52500
70°	37465
75°	20506
80°	3608
85°	0



TEST NUMBER: P857312

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.1	4.9
10°-20°	307.5	13.3
20°-30°	427.0	18.5
30°-40°	465.9	20.2
40°-50°	434.6	18.8
50°-60°	329.9	14.3
60°-70°	180.7	7.8
70°-80°	49.7	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	847.6	36.7
0°-40°	1313.5	56.9
0°-60°	2078.1	90.0
0°-90°	2309.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2309.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1208	
5°	1198	113
15°	1096	307
25°	928	427
35°	745	466
45°	564	435
55°	369	330
65°	181	181
75°	43	50
85°	0	1
90°	0	



TEST NUMBER: P857312

CATALOG NUMBER: LX4C20D010 EX4C209030 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1207.7
2.5°	1207.7
5°	1197.5
7.5°	1182.3
10°	1159.4
12.5°	1128.9
15°	1095.8
17.5°	1055.2
20°	1017.0
22.5°	971.2
25°	928.0
27.5°	884.9
30°	836.4
32.5°	790.7
35°	744.9
37.5°	699.2
40°	655.9
42.5°	610.1
45°	564.3
47.5°	518.7
50°	467.8
52.5°	419.5
55°	368.7
57.5°	320.3
60°	272.1
62.5°	223.7
65°	180.6
67.5°	139.9
70°	104.3
72.5°	71.1
75°	43.2
77.5°	20.3
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)