

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858240

Luminaire Tested: **LX4C45D010 EX4C459835 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459835 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4138.6 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858240

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858240

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265904
5°	264675
10°	259215
15°	249796
20°	238296
25°	225453
30°	212661
35°	200233
40°	188535
45°	175756
50°	160259
55°	141536
60°	119807
65°	94040
70°	67134
75°	36787
80°	6509
85°	0



TEST NUMBER: P858240

CATALOG NUMBER: LX4C45D010 EX4C459835 4LSBH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.7	4.9
10°-20°	551.1	13.3
20°-30°	765.3	18.5
30°-40°	835.1	20.2
40°-50°	779.0	18.8
50°-60°	591.3	14.3
60°-70°	323.8	7.8
70°-80°	89.1	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1519.1	36.7
0°-40°	2354.2	56.9
0°-60°	3724.5	90.0
0°-90°	4138.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4138.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2164	
5°	2146	203
15°	1964	551
25°	1663	765
35°	1335	835
45°	1012	779
55°	661	591
65°	324	324
75°	78	89
85°	0	1
90°	0	



TEST NUMBER: P858240

CATALOG NUMBER: LX4C45D010 EX4C459835 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2164.4
2.5°	2164.4
5°	2146.2
7.5°	2119.0
10°	2077.9
12.5°	2023.3
15°	1964.0
17.5°	1891.1
20°	1822.7
22.5°	1740.7
25°	1663.2
27.5°	1585.8
30°	1499.1
32.5°	1417.2
35°	1335.1
37.5°	1253.1
40°	1175.6
42.5°	1093.6
45°	1011.6
47.5°	929.6
50°	838.5
52.5°	751.8
55°	660.8
57.5°	574.1
60°	487.6
62.5°	401.0
65°	323.5
67.5°	250.6
70°	186.9
72.5°	127.6
75°	77.5
77.5°	36.5
80°	9.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)