

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858253

Luminaire Tested: **LX4C45D010 EX4C459840 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459840 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4143.9 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858253

CATALOG NUMBER: LX4C45D010 EX4C459840 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858253

CATALOG NUMBER: LX4C45D010 EX4C459840 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266248
5°	265021
10°	259552
15°	250126
20°	238597
25°	225738
30°	212945
35°	200488
40°	188776
45°	175965
50°	160469
55°	141707
60°	119954
65°	94186
70°	67206
75°	36834
80°	6509
85°	0



TEST NUMBER: P858253

CATALOG NUMBER: LX4C45D010 EX4C459840 4LSBH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	4.9
10°-20°	551.8	13.3
20°-30°	766.2	18.5
30°-40°	836.1	20.2
40°-50°	780.0	18.8
50°-60°	592.0	14.3
60°-70°	324.2	7.8
70°-80°	89.2	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1521.0	36.7
0°-40°	2357.2	56.9
0°-60°	3729.2	90.0
0°-90°	4143.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4143.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2167	
5°	2149	203
15°	1967	552
25°	1665	766
35°	1337	836
45°	1013	780
55°	662	592
65°	324	324
75°	78	89
85°	0	1
90°	0	



TEST NUMBER: P858253

CATALOG NUMBER: LX4C45D010 EX4C459840 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2167.2
2.5°	2167.2
5°	2149.0
7.5°	2121.7
10°	2080.6
12.5°	2025.9
15°	1966.6
17.5°	1893.6
20°	1825.0
22.5°	1742.9
25°	1665.3
27.5°	1587.8
30°	1501.1
32.5°	1418.9
35°	1336.8
37.5°	1254.7
40°	1177.1
42.5°	1095.0
45°	1012.8
47.5°	930.8
50°	839.6
52.5°	752.8
55°	661.6
57.5°	574.8
60°	488.2
62.5°	401.6
65°	324.0
67.5°	250.9
70°	187.1
72.5°	127.8
75°	77.6
77.5°	36.5
80°	9.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)