

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857360

Luminaire Tested: **LX4C25D010 EX4C259030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259030 4LBMH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1881.9 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857360

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857360

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149034
5°	149603
10°	150048
15°	150056
20°	149237
25°	145734
30°	136213
35°	117956
40°	92151
45°	66108
50°	42946
55°	25703
60°	15037
65°	9651
70°	6430
75°	4842
80°	3608
85°	0



TEST NUMBER: P857360

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	6.1
10°-20°	332.9	17.7
20°-30°	491.2	26.1
30°-40°	484.7	25.8
40°-50°	296.6	15.8
50°-60°	113.7	6.0
60°-70°	35.6	1.9
70°-80°	10.4	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	939.6	49.9
0°-40°	1424.3	75.7
0°-60°	1834.6	97.5
0°-90°	1881.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1881.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1213	
5°	1213	116
15°	1180	333
25°	1075	491
35°	786	485
45°	380	297
55°	120	114
65°	33	36
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P857360

CATALOG NUMBER: LX4C25D010 EX4C259030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1213.1
2.5°	1215.6
5°	1213.1
7.5°	1210.5
10°	1202.8
12.5°	1192.6
15°	1179.8
17.5°	1164.5
20°	1141.5
22.5°	1116.0
25°	1075.1
27.5°	1024.0
30°	960.2
32.5°	881.1
35°	786.5
37.5°	681.8
40°	574.6
42.5°	475.0
45°	380.5
47.5°	296.2
50°	224.7
52.5°	166.0
55°	120.0
57.5°	84.2
60°	61.2
62.5°	46.0
65°	33.2
67.5°	25.6
70°	17.9
72.5°	12.8
75°	10.2
77.5°	5.1
80°	5.1
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)