

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858292

Luminaire Tested: **LD4C10W2N2050D010 4LBNLI_3500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBNLI_3500K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, W2N2050 LEDS AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 798.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858292

CATALOG NUMBER: LD4C10W2N2050D010 4LBNLI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P858292

CATALOG NUMBER: LD4C10W2N2050D010 4LBNLI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252292
5°	227037
10°	176008
15°	127391
20°	88209
25°	64307
30°	46728
35°	27656
40°	11627
45°	3631
50°	478
55°	257
60°	295
65°	349
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858292

CATALOG NUMBER: LD4C10W2N2050D010 4LBNLI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.8	20.3
10°-20°	277.1	34.7
20°-30°	220.2	27.6
30°-40°	116.6	14.6
40°-50°	20.1	2.5
50°-60°	1.5	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.1	82.6
0°-40°	775.7	97.2
0°-60°	797.3	99.9
0°-90°	798.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2054	
5°	1841	162
15°	1002	277
25°	474	220
35°	184	117
45°	21	20
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858292

CATALOG NUMBER: LD4C10W2N2050D010 4LBNLI_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2053.6
2.5°	2000.7
5°	1841.0
7.5°	1632.1
10°	1410.9
12.5°	1197.0
15°	1001.6
17.5°	819.7
20°	674.7
22.5°	564.1
25°	474.4
27.5°	401.9
30°	329.4
32.5°	255.6
35°	184.4
37.5°	121.7
40°	72.5
42.5°	41.8
45°	20.9
47.5°	7.4
50°	2.5
52.5°	2.5
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)