

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857376

Luminaire Tested: **LD4C25D010 EU4259035 4LBMLI**

Issue Date: 7/19/2024

Test Information

Test Method: LM-79-08
Report Number: P857376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25D010 EU4259035 4LBMLI
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2381.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857376

CATALOG NUMBER: LD4C25D010 EU4259035 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857376

CATALOG NUMBER: LD4C25D010 EU4259035 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88		
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78		
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73		
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69		
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65		
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62		
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58		
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461131
5°	453297
10°	416498
15°	348798
20°	279439
25°	224531
30°	167138
35°	95490
40°	44808
45°	19025
50°	6059
55°	3084
60°	2113
65°	1686
70°	1042
75°	0
80°	0
85°	0



TEST NUMBER: P857376

CATALOG NUMBER: LD4C25D010 EU4259035 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.9	14.3
10°-20°	759.8	31.9
20°-30°	755.4	31.7
30°-40°	411.4	17.3
40°-50°	95.1	4.0
50°-60°	13.4	0.6
60°-70°	5.0	0.2
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.0	77.9
0°-40°	2266.4	95.2
0°-60°	2374.9	99.7
0°-90°	2381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2381.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3754	
5°	3676	340
15°	2742	760
25°	1656	755
35°	637	411
45°	110	95
55°	14	13
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P857376

CATALOG NUMBER: LD4C25D010 EU4259035 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3753.5
2.5°	3744.9
5°	3675.7
7.5°	3534.6
10°	3338.7
12.5°	3050.7
15°	2742.4
17.5°	2437.0
20°	2137.4
22.5°	1892.6
25°	1656.4
27.5°	1431.7
30°	1178.2
32.5°	895.9
35°	636.7
37.5°	429.2
40°	279.4
42.5°	175.7
45°	109.5
47.5°	63.4
50°	31.7
52.5°	17.3
55°	14.4
57.5°	8.6
60°	8.6
62.5°	5.8
65°	5.8
67.5°	2.9
70°	2.9
72.5°	2.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)