

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858308

Luminaire Tested: **LD4C10W2N2050D010 4LBWLI_2700K**

Issue Date: 11/9/2023

Test Information

Test Method: LM-79-08
Report Number: P858308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBWLI_2700K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 936.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858308

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858308

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70456
5°	71651
10°	74887
15°	79492
20°	82966
25°	82254
30°	76490
35°	65435
40°	49860
45°	29241
50°	12500
55°	3684
60°	1057
65°	610
70°	395
75°	522
80°	0
85°	0



TEST NUMBER: P858308

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	6.0
10°-20°	177.0	18.9
20°-30°	276.1	29.5
30°-40°	268.7	28.7
40°-50°	134.2	14.3
50°-60°	20.8	2.2
60°-70°	2.5	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.2	54.4
0°-40°	777.8	83.1
0°-60°	932.8	99.7
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	581	56
15°	625	177
25°	607	276
35°	436	269
45°	168	134
55°	17	21
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858308

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	573.5
2.5°	575.6
5°	581.0
7.5°	589.6
10°	600.3
12.5°	614.2
15°	625.0
17.5°	633.5
20°	634.6
22.5°	627.1
25°	606.8
27.5°	576.7
30°	539.2
32.5°	492.1
35°	436.3
37.5°	375.2
40°	310.9
42.5°	242.3
45°	168.3
47.5°	108.3
50°	65.4
52.5°	35.4
55°	17.2
57.5°	7.5
60°	4.3
62.5°	3.2
65°	2.1
67.5°	2.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)