

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857409

Luminaire Tested: **LX4C25D010 EX4C259040 4LBWH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P857409  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259040 4LBWH  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2124.0 lumens  
Efficiency: N/A  
Efficacy: 67.4 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857409

CATALOG NUMBER: LX4C25D010 EX4C259040 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P857409

CATALOG NUMBER: LX4C25D010 EX4C259040 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	168186
5°	168829
10°	169346
15°	169350
20°	168430
25°	164481
30°	153733
35°	133119
40°	104002
45°	74622
50°	48470
55°	29023
60°	16978
65°	10901
70°	7256
75°	5459
80°	4103
85°	0



TEST NUMBER: P857409

CATALOG NUMBER: LX4C25D010 EX4C259040 4LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.4	6.1
10°-20°	375.7	17.7
20°-30°	554.3	26.1
30°-40°	547.0	25.8
40°-50°	334.8	15.8
50°-60°	128.4	6.0
60°-70°	40.1	1.9
70°-80°	11.8	0.6
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1060.4	49.9
0°-40°	1607.4	75.7
0°-60°	2070.6	97.5
0°-90°	2124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2124.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1369	
5°	1369	130
15°	1332	376
25°	1213	554
35°	888	547
45°	430	335
55°	136	128
65°	38	40
75°	12	12
85°	0	2
90°	0	



TEST NUMBER: P857409

CATALOG NUMBER: LX4C25D010 EX4C259040 4LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1369.0
2.5°	1371.9
5°	1369.0
7.5°	1366.2
10°	1357.5
12.5°	1346.0
15°	1331.5
17.5°	1314.2
20°	1288.3
22.5°	1259.5
25°	1213.4
27.5°	1155.7
30°	1083.7
32.5°	994.4
35°	887.6
37.5°	769.5
40°	648.5
42.5°	536.1
45°	429.5
47.5°	334.3
50°	253.6
52.5°	187.4
55°	135.5
57.5°	95.1
60°	69.1
62.5°	51.9
65°	37.5
67.5°	28.8
70°	20.2
72.5°	14.4
75°	11.5
77.5°	5.8
80°	5.8
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)