

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858310

Luminaire Tested: **LD4C10W2N2050D010 4LBWLI_3500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBWLI_3500K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, W2N2050 LEDS AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1073.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858310

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P858310

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80764
5°	82133
10°	85852
15°	91117
20°	95112
25°	94291
30°	87683
35°	75018
40°	57157
45°	33515
50°	14315
55°	4220
60°	1204
65°	727
70°	431
75°	570
80°	0
85°	0



TEST NUMBER: P858310

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	6.0
10°-20°	202.9	18.9
20°-30°	316.5	29.5
30°-40°	308.0	28.7
40°-50°	153.8	14.3
50°-60°	23.8	2.2
60°-70°	2.9	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.7	54.4
0°-40°	891.7	83.1
0°-60°	1069.3	99.7
0°-90°	1073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	657	
5°	666	64
15°	716	203
25°	696	317
35°	500	308
45°	193	154
55°	20	24
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858310

CATALOG NUMBER: LD4C10W2N2050D010 4LBWLI_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	657.4
2.5°	659.9
5°	666.0
7.5°	675.9
10°	688.2
12.5°	704.1
15°	716.4
17.5°	726.3
20°	727.5
22.5°	718.9
25°	695.6
27.5°	661.1
30°	618.1
32.5°	564.1
35°	500.2
37.5°	430.1
40°	356.4
42.5°	277.7
45°	192.9
47.5°	124.1
50°	74.9
52.5°	40.5
55°	19.7
57.5°	8.6
60°	4.9
62.5°	3.7
65°	2.5
67.5°	2.5
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)